

Product data sheet

Characteristics

XZCB4L0050

PvR cable - 4 x 0.5 mm² - length 50 m

Important message: We have updated the process for ordering Telemecanique Sensors products. For more information, please contact your Telemecanique Sensors representative in the UK&I at: UK.salesorders@tesensors.com. You can find all product information on the Telemecanique Sensors website: www.tesensors.com/uk/en
Local distributor code: 388814280
EAN Code: 3389110197235



Main

Accessory / separate part type	Cable
--------------------------------	-------

Complementary

Accessory / separate part designation	Bare cable
Accessory / separate part category	Cabling accessories
Cable length	50 m
Material	PvR (PVC/NBR) sheath
Colour	Matt black
Cable cross section	0.5 mm ²
Total number of wires	4
Wire insulation material	PVC
Flame retardance	Class C2 conforming to NF C 32-070
[Ue] rated operational voltage	300 V
[Ui] rated insulation voltage	2000 V conforming to NF C 32-201-1
Bending radius	Minimum 3 x external diameter
Tensile strength	10...35 N/mm ²
Hardness	70 shores A (tolerance: +/-5)
Net weight	2.22 kg




Environment

Ambient air temperature for operation	-35...90 °C
Ambient air temperature for storage	-40...100 °C
Environmental characteristic	Mineral resistant at 90 °C Without un moulding agent Synthetic oils at 90 °C Soluble resistant at 90 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	23.000 cm
Package 1 Length	23.000 cm
Package 1 Weight	2.250 kg
Unit Type of Package 2	S03
Number of Units in Package 2	4
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	9.246 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------