

# Product data sheet

## Characteristics

# ZBA138

white cap marked IV for circular pushbutton  
Ø22



EAN Code: 3389110091045



### Main

|                                       |                        |
|---------------------------------------|------------------------|
| Accessory / separate part category    | Marking accessory      |
| Accessory / separate part type        | Marked push-button cap |
| Accessory / separate part destination | Push-button head       |
| Language                              | International          |
| Marking                               | Black IV               |
| Cap/operator or lens colour           | White                  |
| Shape of signaling unit head          | Round                  |
| Quantity per set                      | Set of 1               |
| Sale per indivisible quantity         | 10                     |
| Net weight                            | 0.001 kg               |

### Complementary

|                     |   |
|---------------------|---|
| Range compatibility | Harmony XAL<br>Harmony XB4<br>Harmony XB5 |
| Operator profile    | Flush                                     |
| Main group          | Push-button                               |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| RoHS exemption information | <a href="#">Yes</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |
| Circularity Profile        | <a href="#">End Of Life Information</a>  |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|