



Main

Accessory / separate part category	Mounting accessories
Quantity per set	Set of 10
Star-delta starter component	1/4 turn sliding clip nuts and corresponding bolts

Complementary

Assembly style	For assembly
Fixing of mechanism	Screws
Head mounting	M8 x 20
ISO thread	M8
Motor power kW	100 KW 200 KW 185 KW 220 KW 315 KW 250 KW 160 KW 90 KW 280 KW 375 kW
Motor starter type	Star-delta starters
Mounting support	Notched AM1-EC rail
Number of devices	8
Product compatibility	For uprights AM3-EC
Net weight	0.024 Kg 0.023 kg
Shape of screw head	Hexagonal
Threaded length	20 mm
Provided equipment	Washer

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.54 cm
Package 1 Width	2.54 cm
Package 1 Length	2.54 cm
Package 1 Weight	9.072 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	2 cm
Package 2 Width	5 cm
Package 2 Length	13 cm
Package 2 Weight	142 g

Unit Type of Package 3	CAR
Number of Units in Package 3	680
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	10.062 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------