

## Product data sheet

### Characteristics

# NSYS3D5520

Spacial S3D plain door w/o mount.plate.  
H500xW500xD200 IP66 IK10 RAL7035.



Local distributor code: 392866282  
EAN Code: 3606480159398



### Main

|                             |                                                   |
|-----------------------------|---------------------------------------------------|
| Range                       | Spacial                                           |
| Product name                | Spacial S3D                                       |
| Application                 | Multi-purpose                                     |
| Category                    | Compact enclosure                                 |
| Enclosure nominal height    | 500 mm                                            |
| Enclosure nominal width     | 500 mm                                            |
| Enclosure nominal depth     | 200 mm                                            |
| Door type                   | Plain                                             |
| Mounting plate description  | Without mounting plate                            |
| Type of gland plate         | Standard                                          |
| Installation accessory type | Wall-mounting                                     |
| Device composition          | 1 body<br>1 door<br>1 lock<br>1 cable gland plate |

### Complementary

|                             |                                                                      |
|-----------------------------|----------------------------------------------------------------------|
| Body type                   | Single piece body<br>Gutter-shaped front rail double sheet thickness |
| Number of doors             | Front face: 1 door(s)                                                |
| Door opening side           | Reversible (120 °)                                                   |
| Lock type                   | 3 mm double-bar lock                                                 |
| Accessibility for operation | Front                                                                |
| Removable parts             | Door by hinges<br>Cable gland plate by screws                        |
| Material                    | Steel                                                                |
| Surface finish              | Epoxy-polyester powder                                               |
| Colour                      | Grey (RAL 7035)                                                      |
| Standards                   | IEC 62208                                                            |
| Product certifications      | GL[RETURN]cUL[RETURN]LR[RETURN]UL[RETURN]BV[RETURN]DNV               |
| Net weight                  | 9.88 kg                                                              |

### Environment

|                           |                              |
|---------------------------|------------------------------|
| NEMA degree of protection | NEMA 4X/13                   |
| IK degree of protection   | IK10 conforming to IEC 62262 |
| IP degree of protection   | IP66 conforming to IEC 60529 |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 25.5 cm |
| Package 1 Width              | 51.5 cm |
| Package 1 Length             | 51.5 cm |
| Package 1 Weight             | 9.88 kg |
| Unit Type of Package 2       | PAM     |
| Number of Units in Package 2 | 24      |
| Package 2 Height             | 170 cm  |
| Package 2 Width              | 100 cm  |
| Package 2 Length             | 120 cm  |
| Package 2 Weight             | 254 kg  |

## Offer Sustainability

|                            |                                                                                                                                 |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                           |
| REACH Regulation           | <a href="#"> REACH Declaration</a>             |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)                                                                      |
| Mercury free               | Yes                                                                                                                             |
| China RoHS Regulation      | <a href="#"> China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#"> Yes</a>                           |
| Environmental Disclosure   | <a href="#"> Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations                                                                                        |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|