

Product data sheet

Characteristics

NSYTBS292416H

ABS box IP66 IK07 RAL7035

Int.H275W225D160 Ext.H291W241D168

Opaque cover H60



Local distributor code: 387531412

EAN Code: 3606480165399



Main

Range	Thalassa
Product name	Thalassa TBS
Device application	Multi-purpose
Category	Industrial box
Height	291 mm
Width	241 mm
Depth	168 mm
Internal height	275 mm
Internal width	225 mm
Internal depth	160 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Body type	One piece moulded
Type of front cover	High plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

Complementary

Material	ABS (acrylonitrile butadiene-styrene)
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	TÜV
Electrical insulation class	Class II
IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK07 conforming to IEC 62262
Glow wire resistance	650 °C conforming to IEC 60695-2-11
Ambient air temperature for storage	-15...40 °C
Operating temperature	-25...60 °C
Net weight	1.24 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18 cm
Package 1 Width	25 cm
Package 1 Length	30.5 cm
Package 1 Weight	1.207 kg
Unit Type of Package 2	CAR

Number of Units in Package 2	4
Package 2 Height	40 cm
Package 2 Width	40.5 cm
Package 2 Length	60 cm
Package 2 Weight	5.694 kg
Unit Type of Package 3	P12
Number of Units in Package 3	48
Package 3 Height	136 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	77 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------