



## Main

Range of product	Acti 9
Product or component type	Shunt trip release with OC contact
Device short name	IMX+OF
Signal contacts composition	1 C/O
[Ie] rated operational current	AC-12 6 A 12 V AC 50 Hz AC-12 6 A 24 V AC 50 Hz DC-12 6 A 12 V DC DC-12 6 A 24 V DC
[Uc] control circuit voltage	12...24 V AC 50/60 Hz 12...24 V DC
9 mm pitches	2




## Complementary

Range compatibility	Acti 9 iC65 Acti 9 ARA Acti 9 iDPN Vigi Acti 9 iID Acti 9 iSW-NA Acti 9 RCA Acti 9 iDPN (China version) Acti 9 iC60 double terminals miniature circuit breaker Acti 9 iC40
Local signalling	Action indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Width	18 mm
Colour	White
Connections - terminals	Clamp terminal - 2 2,5 mm <sup>2</sup> - flexible with cable end Clamp terminal - 1 6 mm <sup>2</sup> - rigid Clamp terminal - 2 2,5 mm <sup>2</sup> - rigid Clamp terminal - 1 4 mm <sup>2</sup> - flexible
Tightening torque	1 N.m
Compatibility code	IMX+OF

## Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 EN/IEC 60947-5-1
Relative humidity	95 % 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

## Offer Sustainability

Ilgtpējīgs piedāvājuma statuss	Green Premium izstrādājums
REACH regula	 <a href="#">REACH Deklarācija</a>
ES RoHS direktīva	Compliant  <a href="#">ES RoHS Deklarācija</a>
Nesatur toksiskus smagos metālus	Jā
Nesatur dzīvsudrabu	Jā
Informācija par RoHS izņēmumiem	 Jā

Ķīnas RoHS regula	<a href="#">Ķīnas RoHS Deklarācija</a>
Vides informācijas publiskošana	<a href="#">Produkta ietekme Uz Vidi</a>
Cirkularitātes profils	Nav jāveic īpašas darbības, lai nodotu otrreizējai pārstrādei
WEEE	Eiropas Savienības tirgū no šī produkta ir jāatbrīvojas, ievērojot noteiktu atkritumu savākšanas kārtību, un produkts nedrīkst nonākt sadzīves atkritumu tvertnēs.

### Contractual warranty

Garantija	18 months
-----------	-----------