



Main

| | |
|------------------------------|-------------------------|
| Range of product | Acti 9 |
| Product or component type | Undervoltage release |
| Device short name | IMNx |
| [Uc] control circuit voltage | 220...240 V AC 50/60 Hz |
| Control type | With external feeding |
| 9 mm pitches | 2 |

Complementary

| | |
|-------------------------|--|
| Range compatibility | Acti 9 iC65 Acti 9 ARA Acti 9 iDPN Vigi Acti 9 iID Acti 9 iSW-NA Acti 9 RCA Acti 9 iDPN (China version) Acti 9 iC60 double terminals miniature circuit breaker Acti 9 iC40 |
| Local signalling | Action indicator |
| Mounting mode | Clip-on |
| Mounting support | DIN rail |
| Width | 18 mm |
| Colour | White |
| Connections - terminals | Clamp terminal - 1 11 mm ² - rigid Clamp terminal - 2 2,1 mm ² - rigid Clamp terminal - 1 9 mm ² - flexible Clamp terminal - 2 2,1 mm ² - flexible with cable end |
| Tightening torque | 1 N.m |
| Compatibility code | IMNx |

Environment

| | |
|---------------------------------------|--------------------|
| Standards | EN/IEC 60947-5-1 |
| Tropicalisation | 2 EN/IEC 60947-5-1 |
| Relative humidity | 95 % 55 °C |
| Ambient air temperature for operation | -25...50 °C |
| Ambient air temperature for storage | -40...85 °C |

Offer Sustainability

| | |
|---------------------------------|--|
| Ilgspējīgs piedāvājuma statuss | Green Premium izstrādājums |
| REACH regula | REACH Deklarācija |
| ES RoHS direktīva | Atbilstīgs ES RoHS Deklarācija |
| Nesatur dzīvudrabu | Jā |
| Informācija par RoHS izņēmumiem | Jā |
| Ķīnas RoHS regula | Ķīnas RoHS Deklarācija |

| | |
|--------------------------------|--|
| Vides informācijas publicēšana | Produkta Ietekme Uz Vidi |
| Cirkularitātes profils | Informācija Par Eksploatācijas Izbeigšanu |
| WEEE | Eiropas Savienības tirgū no šī produkta ir jāatbrīvojas, ievērojot noteiktu atkritumu savākšanas kārtību, un produkts nedrīkst nonākt sadzīves atkritumu tvertnēs. |

Contractual warranty

| | |
|-----------|-----------|
| Garantija | 18 months |
|-----------|-----------|