

Product data sheet

Characteristics

XAWG130EX

control station - XAW-G - plastic - 1 NO - black
- Start-Stop



Main

Range of product	Harmony XAW
Product or component type	Complete control station
Device short name	XAWG
Control station application	Start-Stop function
Material	Glass fibre reinforced
Control station composition	1 selector switch with standard handle, black 1 NO

Complementary

Colour of base of enclosure	Black
Colour of cover	Black
Cable entry	1 entry for ISO M20 cable gland
Width	80 mm
Depth	70 mm
Height	146 mm
Marking	Ex tb IIIC T85°C Db IP65
Mechanical durability	1000000 cycles
Short-circuit protection	10 A cartridge fuse type gG
[Ie] rated operational current	3 A at 240 V, AC-15, A600 conforming to EN/IEC 60947-5-1 6 A at 120 V, AC-15, A600 conforming to EN/IEC 60947-5-1 0.1 A at 600 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.27 A at 250 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.55 A at 125 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 1.2 A at 600 V, AC-15, A600 conforming to EN/IEC 60947-5-1

Environment

Ambient air temperature for operation	-20...60 °C
Overvoltage category	II conforming to IEC 60536
IP degree of protection	IP65 conforming to IEC 60529
Standards	EN 60079-0:2009 EN 60079-31:2009 EN 60947-5-4 EN 61000-6-2 EN/IEC 60947-1 EN/IEC 60947-5-1 IEC 60079-0:2007 IEC 60079-31:2008
Directives	94/9/EC - ATEX directive
Dust zone	Zone 21 - 22
Product certifications	INERIS 04ATEX0023X

Contractual warranty

Warranty	18 months
----------	-----------