

Product data sheet

Characteristics

XAWG174EX

control station - XAW-G - plastic - 1 NC + 1 NC
- red - Emergency Stop

Main

Range of product	Harmony XAW
Product or component type	Complete control station
Device short name	XAWG
Control station application	Emergency stop function
Material	Glass fibre reinforced
Reset	Turn to release
Control station composition	1 mushroom head Ø 40 mm push-button, red 1 NC + 1 NC

Complementary

Colour of base of enclosure	Black
Colour of cover	Black
Cable entry	1 entry for ISO M20 cable gland
Width	80 mm
Depth	70 mm
Height	146 mm
Marking	II2 D-Ex tb IIIC T85°C Db IP65
Mechanical durability	300000 cycles
Short-circuit protection	10 A cartridge fuse type gG
[Ie] rated operational current	3 A at 240 V, AC-15, A600 6 A at 120 V, AC-15, A600 0.1 A at 600 V, DC-13, Q600 0.27 A at 250 V, DC-13, Q600 0.55 A at 125 V, DC-13, Q600 1.2 A at 600 V, AC-15, A600

Environment

Ambient air temperature for operation	-20...60 °C
IP degree of protection	IP65
Standards	EN 60079-0:2009 EN 60079-31:2009 EN 61000-6-2 IEC 60079-0:2007 IEC 60079-31:2008
Directives	94/9/EC - ATEX directive
Dust zone	Zone 21 - 22
Product certifications	INERIS 04ATEX0023

Contractual warranty

Warranty	18 months
----------	-----------