



Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP unmanaged switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP
Port Ethernet	10BASE-T/100BASE-TX - 5 port(s) copper cable
Maximum number of switches in cascade	Unlimited

Complementary

Integrated connection type	1 M12 port copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E for copper cable
Maximum cable distance between devices	100 m copper cable
Ethernet service	Automatic negotiation of 10/100 Mbit/s and duplex mode Storage and re-routing of received data Auto MDI/MDX
[Us] rated supply voltage	24 V
Supply voltage limits	18...32 V DC SELV
Power consumption in W	3.2 W
Electrical connection	Removable M12 connector 5 ways power supply
Mounting support	35 mm symmetrical DIN rail
Marking	CE
Local signalling	1 LED per channelcopper port activity: 1 LEDpower supply:
Ethernet cabling system	TF switches
Width	60 mm
Height	126 mm
Depth	31 mm
Net weight	0.21 kg

Environment

Ambient air temperature for operation	0...60 °C
IP degree of protection	IP67
Standards	CSA C22.2 No 142 CUL 508

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------