



Main

Range of product	Altivar
Product or component type	Communication module

Complementary

Range compatibility	Altivar Machine ATV320 Altivar 32 Lexium 32
Product compatibility	Lexium 32
Communication port protocol	Modbus TCP Ethernet/IP
Electrical connection	1 connector RJ45, Ethernet/IP 1 connector RJ45, Modbus TCP
Transmission rate	10/100 Mbps
Addressing	IP addressing manual, BOOTP or DHCP
Exchange mode	Half duplex and full duplex
Communication service	Up to 8 connections (includes connections of Modbus TCP/Ethernet IP) for Ethernet IP/Modbus TCP FDR Agent for Ethernet IP/Modbus TCP Read holding registers (03), 63 words max for Modbus TCP Read input registers (04), 63 words max for Modbus TCP Write single register (06) for Modbus TCP Write multiple registers (16), 63 words max for Modbus TCP Read/Write multiple registers (23) for Modbus TCP Read device identification (43) for Modbus TCP Diagnostics (08) for Modbus TCP I/O scanner : read/write, 6 words maximum for Modbus TCP Communication monitoring for Modbus TCP SNMP agent for Ethernet IP Master/Slave hierarchy ODVA AC drive profile and CiA 402 profile for Ethernet IP Fixed communication monitoring adjusted by Ethernet IP scanner adaptor (Master) for Ethernet IP
Web server	Embedded HTTP server
Web services	Ethernet/IP setup Drive parameters Drive monitor Security Ethernet/IP scanner setup Message statistics Ethernet statistics
Display type	1 LED for MS (Module Status) 1 LED for NS (Network Status) 1 LED for Ethernet port activity 1 LED for Modbus TCP port activity
Net weight	0.3 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------