

## Product data sheet

### Characteristics

# NSYBCE8

Spacial SF brush flexible cable entry gaskets -  
25 mm - 800 mm enclosure



#### Main

Range	Spacial
Product or component type	Brush gasket
Accessory / separate part category	Cable management accessory
Device application	Multi-purpose
Range compatibility	Spacial SF suitable enclosure
Device composition	2 gasket
Quantity per set	Set of 1

#### Complementary

Mounting support	Cable gland plate
Cable entry	1 or 2 entries
Fixing mode	Clipped
Height	70 mm
Width	800 Mm nominal: 735 mm real:
Depth	25 mm

#### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

#### Contractual warranty

Warranty	18 months
----------	-----------