

Product data sheet

Characteristics

NSYSFEB

set of 4 Spacial SF M12 lifting eyebolt - galvanized cast steel







Main

Range	Spacial
Category	Lifting accessory
Product or component type	Lifting eye
Application	Multi-purpose
Mounting location	Enclosure top
Mounting support	Directly in the axis of the uprights
Range compatibility	Spacial SF Spacial SFHD Prisma PH Spacial SFM
Device composition	4 eyebolt
Quantity per set	Set of 1

Complementary

Material	Cast steel
Surface finish	Galvanized
Fixing mode	Screwed
Permanent permissible load	1360 kg slinging at 60°
Height	62.5 mm
Width	55 mm
Depth	24 mm
Diameter	29 mm
ISO thread	M12

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.