

Product data sheet

Characteristics

GV2LC02

empty enclosure without starter GV2-LC



Main

Range of product	TeSys
Device short name	GV2LC
Motor starter type	Non reversing
Product or component type	Enclosure without starter with rotary handle mounted on cover
Poles description	3P
Motor starter composition	Without circuit breaker
Thermal protection adjustment range	1.6...18 A
Control type	Rotary handle black
Enclosure material	Polycarbonate

Complementary

Cable entry	2 x 20 mm ISO at bottom 2 x 20 mm ISO at top 2 x 25 mm ISO at bottom 2 x 25 mm ISO at top
Width	88 mm
Height	166 mm
Depth	173 mm
Net weight	0.3 kg

Environment

Standards	EN 60947 IEC 60439-1 VDE 0660-102 IEC 60947-4
IP degree of protection	IP547 conforming to IEC 60529

Contractual warranty

Warranty	18 months
----------	-----------