

## Product data sheet

### Characteristics

## EZEAX

### auxiliary contact - for Easypact EZ250



#### Main

Range of product	EZC250 EZCV250
Range	EasyPact
Device short name	AX
Product or component type	Switch
Device application	Signalling
Range compatibility	EasyPact EZC circuit breaker EasyPact EZCV circuit breaker
Signal contacts composition	1 NO/NC



#### Complementary

Auxiliary contacts type	Standard
[I <sub>th</sub> ] conventional free air thermal current	5 A
[I <sub>e</sub> ] rated operational current	AC-12: 3 A at 250 V AC 50/60 Hz AC-12: 5 A at 125 V AC 50/60 Hz AC-12: 5 A at 24 V AC 50/60 Hz AC-12: 5 A at 48 V AC 50/60 Hz AC-15: 2 A at 250 V AC 50/60 Hz AC-15: 3 A at 125 V AC 50/60 Hz AC-15: 5 A at 24 V AC 50/60 Hz AC-15: 5 A at 48 V AC 50/60 Hz DC-12: 0.2 A at 250 V DC DC-12: 0.4 A at 125 V DC DC-12: 2.5 A at 48 V DC DC-12: 4 A at 24 V DC DC-14: 0.2 A at 250 V DC DC-14: 0.4 A at 125 V DC DC-14: 1 A at 48 V DC DC-14: 3 A at 24 V DC
Minimum load	10 mA at 24 V
Auxiliary connection terminal	Lead wire

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.1 cm
Package 1 Width	3.3 cm
Package 1 Length	8.8 cm
Package 1 Weight	40.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	105
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.687 kg

Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	 <a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 개월
----------	-------