



Hoofd

Range	TeSys
Device short name	LA4K
Product or component type	Onderdrukkingsmodule
Compatibiliteit product	LC1K LP1K LP4K CA2K CA3K

Complementair

Montagezone	Voorzijde
Mounting mode	Clip-on
Ontstoringstechnologie	Varistor (piekbegrenzing)
Spanning stuurkring	50...129 V AC 50...129 V DC
Maximum piekspanning	2 Uc
Lokale signalering	LED
Quantity per set	Set van 5
Height	26 mm
Width	6 mm
Depth	22 mm
Net weight	0,01 kg

Omgeving

Standards	UL 60947-5-1 CSA C22.2 Nr 60947-5-1 EN/IEC 60947-5-1
Product certifications	UL[RETURN]CSA[RETURN]CE[RETURN]UKCA
IP beschermingsgraad	IP2x conform aan IEC 60529
Beschermende behandeling	TC conform aan IEC 60068 TC conform aan DIN 50016
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-50...80 °C

Verpakkingseenheid

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0,500 cm
Package 1 Width	2,600 cm
Package 1 Length	3,900 cm
Package 1 Weight	5,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	2,800 cm

Package 2 Width	4,200 cm
Package 2 Length	5,100 cm
Package 2 Weight	27,000 g
Unit Type of Package 3	S01
Number of Units in Package 3	420
Package 3 Height	15,000 cm
Package 3 Width	15,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	2,537 kg

Duurzaamheid van het aanbod

Duurzaamheids status van het aanbod	Green Premium product
REACH-regelgeving	 REACH-verklaring
REACH vrij van SVHC	Ja
EU-richtlijn RoHS	Voldoet aan vrijstellingen
Vrij van giftige zware metalen	Ja
Kwikvrij	Ja
RoHS-regulering China	 RoHS-verklaring China
Informatie over RoHS-vrijstelling	 Ja
Milieu Profiel	 Milieuprofiel Van Het Product
Circulair Profiel	Geen specifieke recycling vereist
WEEE	Het product moet op markten van de Europese Unie worden afgevoerd volgens specifieke afvalinzamelingsregels en mag nooit in een gewone vuilnisbak terechtkomen.

contractuele waarborg

Garantie	18 months
----------	-----------