

Product data sheet

Characteristics

13392

mini Opale surface enclosure - IP 30 - 1 x 2 modules - without door



Main

Product or component type	Enclosure
Enclosure type	Distribution enclosure
Nb of 18 mm modules per row	2
Standards	IEC 60529 EN 50102
Colour	Enclosure: white (RAL 9003)

Complementary

Enclosure mounting	Surface
Nb of horizontal rows	1
[In] rated current	63 A
Type of rail	DIN
Mounting plate description	Without mounting plate
Enclosure material	Enclosure: self-extinguishing material
Width	44 mm
Height	130 mm
Depth	57 mm
Internal depth	52 mm

Environment

IP degree of protection	IP30 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.300 cm
Package 1 Width	4.400 cm
Package 1 Length	13.100 cm
Package 1 Weight	70.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	14.400 cm
Package 2 Width	12.000 cm
Package 2 Length	25.000 cm
Package 2 Weight	750.000 g
Unit Type of Package 3	P12
Number of Units in Package 3	1960

Package 3 Height	80.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	158.020 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------