

Product data sheet

Characteristics

20CJB4W

2-way angle box - for 20 mm conduit - white



Main

Range of product	Mita
Product or component type	Junction box
Colour tint	White
Quantity per set	Set of 20

Complementary

Cable entry	2 tube entry
Junction box type	Angle
Product destination	Diameter: 20 mm conduit
Product compatibility	Insert clip when used to suspend lighting units
Maximum load	3 kg at 60 °C
Material	UPVC (unplasticized polyvinyl chloride)

Environment

Standards	BS 4607-5
-----------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.290 cm
Package 1 Width	7.290 cm
Package 1 Length	7.290 cm
Package 1 Weight	47.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	18.000 cm
Package 2 Width	18.000 cm
Package 2 Length	24.000 cm
Package 2 Weight	1.084 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	2880
Package 3 Height	115.000 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	151.344 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------