

Product data sheet

Characteristics

GFOPLATE

Exclusive - flex outlet - front entry - 20A - white



Main

Range of product	Exclusive
Product or component type	Flex outlet
Device presentation	Complete product
Colour tint	White
Quantity per set	Set of 10

Complementary

Cable entry	Front entry
Fixing mode	By screws
Rated current	20 A
Number of gangs	1 gang
Material	Urea (carbamide)
Surface finish	Matt
Height	86 mm
Width	86 mm
Depth	18 mm
Net weight	0.086 kg

Environment

Standards	BS 1363
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	8.5 cm
Package 1 Length	2 cm
Package 1 Weight	90 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.4 cm
Package 2 Width	11.1 cm
Package 2 Length	18.3 cm
Package 2 Weight	996.8 g
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	24 cm
Package 3 Width	38.5 cm

Package 3 Length	50 cm
Package 3 Weight	19.86 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------