

Product data sheet

Characteristics

GSKTSW3G

Exclusive Square edge white moulded -
switched and fused socket - 13 A - 230 V



Main

Range of product	Exclusive
Aesthetic name	Square edge white moulded
Product or component type	Switched and fused socket
Device presentation	Complete product
Outlet standard	British
Colour tint	White matt
Quantity per set	Set of 5

Complementary

Switch function	1-pole
Rated current	13 A at 230 V AC 50 Hz
Actuator	Rocker
Number of gangs	3 gangs
Pilot light	Without neon indicator
Fixing mode	By screws
Connections - terminals	Screw terminals
Material	Urea (carbamide)
Type of installation	Indoor
Depth	31 mm
Width	205 mm
Height	86 mm
Net weight	0.332 kg

Environment




Standards	BS 1363
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	337.5 g
Package 1 Height	3 cm
Package 1 Width	8.6 cm
Package 1 Length	20.6 cm
Unit Type of Package 2	PAM
Number of Units in Package 2	1200
Package 2 Weight	455.161 kg
Package 2 Height	110.5 cm
Package 2 Width	100 cm
Package 2 Length	120 cm

Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Weight	1.767 kg
Package 3 Height	9.4 cm
Package 3 Width	15.7 cm
Package 3 Length	22 cm

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------