

Product data sheet

Characteristics

MFA2W

mini trunking - flat bend - 25 x 16 mm



Main

Product or component type	Bend
Colour tint	White
Quantity per set	Set of 10

Complementary

Trunking dimension	25 x 16 mm
Fixing mode	By coupling
Material with surface finish	UPVC (unplasticized polyvinyl chloride)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.800 cm
Package 1 Width	4.800 cm
Package 1 Length	4.800 cm
Package 1 Weight	8.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5.500 cm
Package 2 Width	11.000 cm
Package 2 Length	13.000 cm
Package 2 Weight	88.000 g
Unit Type of Package 3	CAR
Number of Units in Package 3	1500
Package 3 Height	39.000 cm
Package 3 Width	52.000 cm
Package 3 Length	58.000 cm
Package 3 Weight	14.610 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Contractual warranty	
Warranty	18 months