

Product data sheet

Characteristics

XACA9413

round head for pushbutton - spring return -
XAC-A - green - booted



Main

Range of product	Harmony XAC
Product or component type	Head for push-button
Component name	XACA

Complementary

Marking	Unmarked
Operator additional information	Booted
Cap/operator or lens colour	Green
Product compatibility	XACA..
Mounting location	Front of enclosure
Sale per indivisible quantity	10
Standards	IEC 60947-5-1 CSA C22.2 No 14 UL 508 IEC 60204-32
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262
Net weight	0.01 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	14.0 cm
Package 1 Length	17.0 cm
Package 1 Weight	9.0 g
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	3.0 cm
Package 2 Width	7.5 cm
Package 2 Length	11.0 cm
Package 2 Weight	94.0 g
Unit Type of Package 3	S03

Number of Units in Package 3	700
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	7.068 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------