

Product data sheet

Characteristics

A9Z05425

Residual current circuit breaker (RCCB), Acti9
ID K, 4P, 25A, AC type, 30mA



Main

Range	Acti9
Product name	Acti9 ID K
Product or component type	Residual current circuit breaker (RCCB)
Device short name	ID K
Poles description	4P
Neutral position	Left
[In] rated current	25 A
Network type	AC
Earth-leakage sensitivity	30 MA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Quality labels	VDE

Complementary

Device location in system	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	380...415 V AC 50 Hz
Residual current tripping technology	Voltage independent
Rated breaking and making capacity	Idm 500 A Im 500 A
Rated conditional short-circuit current	GL63: Inc 4.5 kA K60: Inc 6 kA
[Ui] rated insulation voltage	440 V AC 50 Hz
[Uimp] rated impulse withstand voltage	4 KV
Surge current	250 A
Contact position indicator	No
Control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	81 Mm
Width	72 Mm
Depth	68 Mm
Colour	White
Mechanical durability	5000 Cycles
Electrical durability	AC-1: 2000 cycles
Connections - terminals	Biconnect top or bottom 1...35 mm ² rigid Biconnect top or bottom 1...25 mm ² flexible
Wire stripping length	14 Mm for top or bottom connection
Tightening torque	3.5 N.M top or bottom

Environment

Standards	EN/IEC 61008-1 EN/IEC 61008-2-1
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	2
Electromagnetic compatibility	8/20 µs impulse withstand, 200 A conforming to EN/IEC 61008-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-30...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 Cm
Package 1 Width	8.500 Cm
Package 1 Length	9.000 Cm
Package 1 Weight	349.000 G
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	30.000 Cm
Package 2 Width	30.000 Cm
Package 2 Length	40.000 Cm
Package 2 Weight	9.529 Kg
Unit Type of Package 3	P12
Number of Units in Package 3	216
Package 3 Height	45.000 Cm
Package 3 Width	80.000 Cm
Package 3 Length	120.000 Cm
Package 3 Weight	90.560 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------