

Tehničke karakteristike proizvoda

Karakteristike

13175

Mureva - za utičnice- 1 otvor - 1 x 4 modula - 1 priključni blok



Osnovne informacije

Grupa proizvoda	Mureva
Ime proizvoda	Mureva Enclosure
Tip proizvoda ili komponente	Orman
Tip ormana	Orman za utičnice
Opis montažne ploče	Bez montažne ploče

Dopunske informacije

Montaža ormana	Površinska
9 mm redovi	8
Broj 18 mm modula po redu	4
Ukupan broj 18 mm modula	4
Broj horizontalnih redova	1
Električna klasa izolacije	Dupla izolacija Klasa II
Broj otvora interfejsa	1
Tip prednjeg poklopca	Providni
Snaga disipacije u w	10 W
[in] nazivna struja	63 A
Tip šine	DIN
Broj otvora pg iso	1
Opis opcija zaključavanja	Opciona bravica
Materijal kućišta	Kućište: samogasivi polimer
Masa proizvoda	0,425 kg
Dimenzija baze	65 x 85 mm
Širina	98 mm
Visina	248 mm
Dubina	98 mm
Unutrašnja dubina	61 mm
Boja	Vrata: prozirnazelena Orman: svetlosiva (RAL 7035)

Okruženje

Standardi	EN 62262 IEC 60695-2-1 IEC 61439-3 EN 50262 IEC 60670
Otpornost na vatru	650 °C u skladu sa IEC 60695-2-1
Ip stepen zaštite	IP65 u skladu sa IEC 60529
Ik stepen zaštite	IK09 u skladu sa EN 50102
Environmental characteristics (UV)	UV otpornost: klasa 3 u skladu sa ISO 4582:2010 Test ultraljubičaste degradacije u skladu sa ISO 4892-2:2013
Kategorija prenapona	II
Temperatura okoline za rad uređaja	-25...40 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9,700 cm
Package 1 Width	9,800 cm
Package 1 Length	24,500 cm
Package 1 Weight	395,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	21,800 cm
Package 2 Width	34,300 cm
Package 2 Length	40,000 cm
Package 2 Weight	3,400 kg
Unit Type of Package 3	P12
Number of Units in Package 3	192
Package 3 Height	100,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	94,392 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Učinak u vezi sa sadržajem halogena	Proizvod bez halogena
Minimum percentage of recycled plastic content	26

Ugovorna garancija

Garancija	18 meseci
-----------	-----------