

Product data sheet

Characteristics

14911

Vertical Comb Busbar 1P+N 18mm distance 150mm



Principal

Gama	Linergy
Nume produs	FV
Tip produs sau componenta	Vertical comb busbar
Mod de montare	Vertical
Descriere poli	1P + N
Numar de cai	1 way pentru top N + L cu 18 mm pas 1 way pentru bottom N + L cu 18 mm pas
Height pitch dimension	150 mm
Pas de conectare	18 mm top - 18 mm bottom

Suplimentar

Cantitate pe set	Set de 1
Dispozitiv de sosire	ID on enclosure
[In] curent nominal	80 A 40 °C)
[Ue] tensiune nominala de functionare	230 V c.a. 50/60 Hz Ph/N 415 V c.a. 50/60 Hz Ph/Ph
[Ui] tensiune nominala de izolatie	500 V c.a. 50/60 Hz conformitate cu IEC 60439-1
[Uimp] tensiune nominala de tinere la impuls	6 kV conformitate cu IEC 60439-1
Pieptene bare de distributie pe categorii de compatibilitate	DuoLine XE DuoLine XP 63 A
Standarde	SR EN 60664-1
Inaltime	165 mm
Latime	37 mm
Adancime	25 mm
Culoare	Gri antracit (RAL 7016)
Compatibilitate gama	DuoLine Pragma Domae
Compatibilitate produs	ID'clac ID R'clacXE Opale I ID'clac XE ID'clac XP

Mediu

Rezistenta la foc	850 °C 30 s) conformitate cu IEC 60695-2-1
-------------------	---

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. It is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	3 cm
Latime prima forma de impachetare	3,5 cm
Lungime prima forma de impachetare	17 cm
Greutate prima forma de impachetare	0,084 kg

Sustenabilitatea ofertei

Regulamentul REACH	 Declaratia REACH
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conform  Declaratia RoHS UE
Fara metale grele toxice	Da
Fara mercur	Da
Regulamentul RoHS China	 Declaratia RoHS China
Informatii privind scutirea de la RoHS	 Da
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.