

## Product data sheet

### Characteristics

# A9N26923

## Acti 9 -Contact Auxiliar Ofs 1 O/C For Rccb



### Principal

Gama de produse	Acti 9 Clario Prodis Librio
Tip produs sau componenta	Contact comutator
Nume scurt al dispozitivului	OFS
Compozitie contacte de semnalizare	1 C/O
[In] curent nominal	3 A 380...415 V c.a. - 50/60 Hz 6 A 220...240 V c.a. - 50/60 Hz 1 A 130 V c.c. 1,5 A 60 V c.c. 2 A 48 V c.c. 6 A 24 V c.c.
Pasi de 9 mm	1

### Suplimentar

Compatibilitate gama	Acti 9 RCCB-ID Acti 9 ID C40 Acti 9 IDc Acti 9 ITG40
Mod de montare	Fix
Suport de montare	Sina DIN
Inaltime	85,3 mm
Latime	9 mm
Adancime	78,5 mm
Greutate produs	33 g
Culoare	Alb
Conexiuni - borne	Borna cu clema (partea inferioara) 2 cablu(ri) 1,5 mm <sup>2</sup> - flexibil Borna cu clema (partea inferioara) 1 cablu(ri) 0,5...2,5 mm <sup>2</sup> - rigid Borna cu clema (partea inferioara) 2 cablu(ri) 1,5 mm <sup>2</sup> - flexibil cu ferula
Lungimea de dezizolare a cablului	9 mm
Cuplu de strangere	1 N.m

### Mediu




Standarde	SR EN 60947-5-1
Grad de protectie IP	IP20 conformitate cu SR EN 60947-5-1
Grad de poluare	3 conformitate cu SR EN 60947-5-1
Tropicalizare	2 conformitate cu SR EN 60947-5-1
Umiditate relativa	0,95 % la 55 °C
Temperatura ambientală de functionare	-35...70 °C
Temperatura de depozitare	-40...85 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Tip unitate a formei de impachetare 1	PCE
Număr de produse în pachet	1
Greutate colet(Lbs)	42 g
Înălțimea formei de impachetare 1	2 cm
Latimea formei de impachetare 1	7,8 cm
Lungimea formei de impachetare 1	9,3 cm
Tip unitate a formei de impachetare 2	S03
Numar de unitati in forma de impachetare 2	108
Greutatea formei de impachetare 2	5,688 kg
Înălțimea formei de impachetare 2	30 cm
Latimea formei de impachetare 2	30 cm
Lungimea formei de impachetare 2	40 cm
Tip unitate a formei de impachetare 3	BB1
Numar de unitati in forma de impachetare 3	12
Greutatea formei de impachetare 3	631 g
Înălțimea formei de impachetare 3	10 cm
Latimea formei de impachetare 3	9 cm
Lungimea formei de impachetare 3	26 cm

## Offer Sustainability

Directiva RoHS UE	Conform  <a href="#">Declaratia RoHS UE</a>
Fara metale grele toxice	Da
Fara mercur	Da
Informatii privind scutirea de la RoHS	 Da
Regulamentul RoHS China	 <a href="#">Declaratia RoHS China</a>
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.

## Contractual warranty

Garantie	18 months
----------	-----------