

Product data sheet

Characteristics

DF2LN1251

Patron Siguranta Din 4 Cu Lame - Gg 1250 A - Fara Indicatie



Principal

Gama de produse	DF
Tip produs sau componenta	Sigurante
Nume scurt al dispozitivului	Siguranta lamelara
[Ue] tensiune nominala de functionare	500 V c.a.
Dimensiune siguranta fuzibila	NH4
Tip siguranta	DIN

Suplimentar

[In] curent nominal	1250 A
Curba siguranta	GG
Cantitate pe set	Set de 1
Greutate neta	1,9 kg

Packing Units

Greutate colet(Lbs)	2,434 kg
Inaltimea formei de impachetare 1	0,960 dm
Latimea formei de impachetare 1	1,270 dm
Lungimea formei de impachetare 1	2,870 dm

Offer Sustainability

Stare ofertă sustenabilă	Produs Green Premium
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conform Declaratia RoHS UE
Fara metale grele toxice	Da
Fara mercur	Da
Informatii privind scutirea de la RoHS	Da
Regulamentul RoHS China	Declaratia RoHS China
Raport de mediu	Profilul Ambiental Al Produsului
Fara PVC	Da

Garantie contractuală

Garantie	18 luni
----------	---------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.