

Product data sheet

Characteristics

MGU3.466.18

Unica, Izolatie Tv Simpla, Mama de Trecere, 2 M, Alb



Principal

Gama	Unica
Denumire	Unica (standard estetic)
Tip produs sau componenta	Priza TV
Prezentare dispozitiv	Mecanism
Tip priza TV	De trecere
Culoare	Alb

Suplimentar

Conector TV	IEC 9,52 mm mamă
Atenuare maxima pe ramura	TV <0,5 dB
Atenuare traseu	11 dB TV semnal5...862 MHz
Flux de curent c.c.	Nu
Numar pe linie	4
Numar module	2 module
Material	ASA + PC: capac mecanism
Mod de fixare	Clipsare
Adancime	28 mm
Latime	45 mm
Inaltime	45 mm
Adancime de montaj	18 mm
Greutate neta	0,073 kg

Mediu

Grad de protectie IP	IP20
Grad de protectie IK	IK01
Temperatura ambientala de functionare	15...35 °C
Temperatura ambietala pentru depozitare	0...35 °C
Caracteristica de mediu	Alcool Acetona Benzina Decolorant Fluid de curatare a geamurilor Ulei Rezistent UV Sapun lichid
Standarde	EN 50083-4 EMC Directiva de compatibilitate electromagnetica EN 50083-1 EN 50083-2

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	6,7 cm
Latime prima forma de impachetare	3,8 cm
Lungime prima forma de impachetare	6,8 cm
Greutate prima forma de impachetare	52,0 g
Unitate de masura pentru a doua forma de impachetare	CAR
Numar unitati in a doua forma de impachetare	10
Inaltime a doua forma de impachetare	33,5 cm
Latime a doua forma de impachetare	4,4 cm
Lungime a doua forma de impachetare	13,6 cm
Greutate a doua forma de impachetare	520,0 g

Sustenabilitatea ofertei

Regulamentul REACH	Declaratia REACH
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conform Declaratia RoHS UE
Fara metale grele toxice	Da
Fara mercur	Da
Regulamentul RoHS China	Declaratia RoHS China
Informatii privind scutirea de la RoHS	Da
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.

Garanție contractuală

Garantie	18 luni
----------	---------