

Product data sheet

Characteristics

MGU5.512.25ZD

Unica, rotary dimmer, 230 VAC, 40...1000 W/
VA, ivory



Principal

Denumire	Unica (standard estetic)
Tip produs sau componenta	Variator de tensiune
Prezentare dispozitiv	Mecanism cu suport de fixare
Mod de fixare	Suruburi
[Ue] tensiune nominala	230 V c.a. 50 Hz
Numar module	2 module
Culoare	Fildes

Suplimentar

Comanda variator	Tip buton rotativ cu apasare
Curent maxim permanent	2,6 A
Numarul total de conductoare	3
Tip de sarcina	Lampa cu halogen 230 V c.a. - 40...1000 W Lampa cu incandescenta 230 V c.a. - 40...1000 W Lampa cu halogen de tensiune scazuta cu transformator feromagnetic (netoroidal) - 40...1000 VA 230 V AC motor - 60...600 W
Tip de protectie	Protectie electronica la supratensiune Protectie curent
Marcaj	L+N
Conexiuni - borne	Borne cu surub
Capacitate conexiune de prindere	$\leq 2 \times 2.5 \text{ mm}^2$
Material	ASA + PC: capac mecanism Zamak: suport de fixare
Standarde	EN 60669-2-1
Certificari produs	UE[RETURN]AENOR
Temperatura ambientala de functionare	5...30 °C
Temperatura ambietala pentru depozitare	-20...60 °C
Adancime de montaj	34 mm
Adancime	54 mm
Latime	70,9 mm
Inaltime	70,9 mm
Greutate neta	0,1215 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mediu

Grad de protectie IK	IK01
Grad de protectie IP	IP20
Caracteristica de mediu	Decolorant Alcool Sapun lichid Rezistent UV Benzina Ulei Acetona Fluid de curatare a geamurilor

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	6,500 cm
Latime prima forma de impachetare	9,800 cm
Lungime prima forma de impachetare	10,800 cm
Greutate prima forma de impachetare	172,900 g
Unitate de masura pentru a doua forma de impachetare	S02
Numar unitati in a doua forma de impachetare	15
Inaltime a doua forma de impachetare	15,000 cm
Latime a doua forma de impachetare	30,000 cm
Lungime a doua forma de impachetare	40,000 cm
Greutate a doua forma de impachetare	2,945 kg

Sustenabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Regulamentul REACH	Declaratia REACH
Directiva RoHS UE	Conform cu anumite exceptii
Fara mercur	Da
Regulamentul RoHS China	Declaratia RoHS China
Informatii privind scutirea de la RoHS	Da
Raport de mediu	Profilul Ambiental Al Produsului
Profil circularitate	Informatii Privind Sfarsitul Duratei De Viata
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.

Garanție contractuală

Garantie	18 luni
----------	---------