

Product data sheet

Characteristics

NSYPAPLA75

internal door for PLA enclosure H750xW500 mm



Principal

Gama	Thalassa
Categorii accesorii / piese de schimb	Accesoriu cofret
Tip produs sau componenta	Usa
Aplicatie	Multifunctional
Pentru dimensiunile nominale ale carcasei	-
Locul de montare	Partea frontala
Compatibilitate gama	Thalassa (Thalassa PLA)
Compozitie dispozitiv	1 uşă Elemente de fixare Insert de bronz M8

Suplimentar

Material	Aluminiu
Culoare	Gri (RAL 7032)
Tip incuietoare	Blocare 5mm bara dubla
Numar de incuietori	2
Tip usa	Plan interior
Parte de deschidere usa	Stanga (110 °)
Inaltime	648 mm
Latime	398 mm
Adancime	Adancime disponibila intre usa:30 mm

Garanție contractuală

Garantie	18 luni
----------	---------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.