

Product data sheet

Characteristics

NSYCRN46250

Spacial CRN plain door w/o mount.plate.
H400xW600xD250 IP66 IK10 RAL7035..



Main

Range	Spacial
Product name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	400 Mm
Enclosure nominal width	600 Mm
Enclosure nominal depth	250 Mm
Installation accessory type	Wall-mounting
Device composition	1 body 1 cable gland plate 1 door 1 lock
Door type	Plain
Mounting plate description	Without mounting plate

Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Body: steel
Surface finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	cUL[RETURN]UL[RETURN]DNV-GL
Net weight	10.816 Kg

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	26.500 Cm
Package 1 Width	41.000 Cm
Package 1 Length	61.500 Cm
Package 1 Weight	10.459 Kg
Unit Type of Package 2	PAM
Number of Units in Package 2	27
Package 2 Height	220.000 Cm
Package 2 Width	100.000 Cm
Package 2 Length	120.000 Cm
Package 2 Weight	295.393 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------