

Product data sheet

Characteristics

PKZM709

Multiple adapter, Mureva PK, 3x16A, 220V, 2P +E, IP67



Main

Range	Mureva
Product or component type	Multiple adapter
Accessory / separate part category	Adaptation accessory
Poles description	2P + E

Complementary

[In] rated current	16 A
[Ue] rated operational voltage	220 V
Socket number	3 (16 A)
Contacts material	Pins: nickel plated brass Sleeves: brass
Plug, socket material	Housing: self-extinguishing polymer
Net weight	0.61 Kg
Height	222 Mm
Width	233 Mm
Colour	Grey (RAL 7035)
Voltage colour	Blue

Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-11
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 Cm
Package 1 Width	20.1 Cm
Package 1 Length	23.6 Cm
Package 1 Weight	612.0 G
Unit Type of Package 2	S03
Number of Units in Package 2	9
Package 2 Height	30.0 Cm

Package 2 Width	30.0 Cm
Package 2 Length	40.0 Cm
Package 2 Weight	5.995 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------