

Product data sheet  
Characteristics

XZCRTPA8

jumper cable - male/female M8 - cable 2580 mm



Main

Accessory / separate part designation	Male/female M8 jumper cable
Accessory / separate part destination	Preventa safety mats
Accessory / separate part category	Connection accessories
Accessory / separate part type	Jumper cable
Cable length	2580 mm

Complementary

Cable outer diameter	4.5 mm
Electrical connection	1 female connector M8 straight 1 male connector M8 straight
Contact resistance	15 mOhm
Insulation resistance	> 100000000 Ohm
Cable composition	2 x 0.5 mm <sup>2</sup>
[In] rated current	4 A
[Ue] rated operational voltage	60 V AC 60 V DC
Net weight	0.06 kg

Environment

Ambient air temperature for operation	-25...90 °C
IP degree of protection	IP68

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.