

Product data sheet

Characteristics

LMR7724038

Easy Styl, Rama inox, 4M, bronz/crom



Principal

Gama	Easy Styl
Tip produs sau componenta	Rama decorativa
Prezentare dispozitiv	Element de baza
Culoare	Bronz

Suplimentar

Compatibilitate gama	Easy Styl
Material	Inox
Numar module	4 module
Inaltime	86 mm
Adancime	9,5 mm
Latime	148 mm
Mod de fixare	Clipsare
Greutate neta	1,12 kg

Mediu

Grad de protectie IP	IP20
----------------------	------

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	1,500 cm
Latime prima forma de impachetare	9,000 cm
Lungime prima forma de impachetare	14,500 cm
Greutate prima forma de impachetare	112,000 g
Unitate de masura pentru a doua forma de impachetare	BB1
Numar unitati in a doua forma de impachetare	10
Inaltime a doua forma de impachetare	8,500 cm
Latime a doua forma de impachetare	14,000 cm
Lungime a doua forma de impachetare	26,000 cm
Greutate a doua forma de impachetare	1,185 kg
Unitate de masura pentru a treia forma de impachetare	S04
Numar unitati in a treia forma de impachetare	100
Inaltime a treia forma de impachetare	30,000 cm
Latime a treia forma de impachetare	40,000 cm

Lungime a treia forma de impachetare	60,000 cm
Greutate a treia forma de impachetare	12,450 kg

Sustenabilitatea ofertei

Directiva RoHS UE	Conform cu anumite exceptii
Regulamentul RoHS China	 Declaratia RoHS China
Informatii privind scutirea de la RoHS	 Da

Garantie contractuala

Garantie	18 luni
----------	---------