



Principal

Gama de produse	Unica
Denumire	Unica Top - Unica Class
Tip produs sau componenta	Intreruptor cu revenire
Prezentare dispozitiv	Mecanism
Tip tehnologie	Electromecanic
Functie de comutare	Simplu
Numar de clapete	1
Aplicatie a dispozitivului	Intreruptor cu simbol sonerie
Culoare	Grafit

Suplimentar

Curent nominal	10 A
[Ue] tensiune nominala	250 V
Tip retea electrica	C.a.
Frecventa retea electrica	50/60 Hz
Durabilitate electrica	40000 cic, cos phi = 0,6
Rezistenta de izolatie	> 5 MΩ la 500 V
Rigiditate dielectrica	2000 V
Capacitatea de rupere la sarcina minima	200 operatii 1.25 In si 1.1 Un, cos phi = 0,3
Conditii de utilizare	Relev de comandă cu impuls
Distanța de deschidere	> 3 mm
Actuator	Intreruptor cu revenire
Numar module	1 modul
Conexiuni - borne	Borna fara surub
Sectiune cablu	0...2,5 mm ² rigid cablu 0...2,5 mm ² flexibil cablu
Material	ABS (nitril acrilic butadiena - stirena): capac mecanism
Marcaj	Simbol sonerie
Mod de fixare	Clipsare
Latime	22,5 mm
Inaltime	45 mm
Adancime	34 mm
Adancime de montaj	22 mm
Greutate neta	0,0173 kg
Temperatura ambientala de functionare	25...35 °C
Temperatura ambietala pentru depozitare	0...50 °C
Standarde	Directiva de joasa tensiune EN 60669-1 EMC Directiva de compatibilitate electromagnetica

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mediu

Grad de protectie IP	IP20
Grad de protectie IK	IK01
Caracteristica de mediu	Fluid de curatare a geamurilor Alcool Benzina Decolorant Sapun lichid Acetona Rezistent UV Ulei

Unitati de ambalare

Unitate de masura pentru prima forma de impachetare	PCE
Numar unitati in prima forma de impachetare	1
Inaltime prima forma de impachetare	6,7 cm
Latime prima forma de impachetare	4,4 cm
Lungime prima forma de impachetare	6,8 cm
Greutate prima forma de impachetare	28,0 g
Unitate de masura pentru a doua forma de impachetare	CAR
Numar unitati in a doua forma de impachetare	10
Inaltime a doua forma de impachetare	33,5 cm
Latime a doua forma de impachetare	4,4 cm
Lungime a doua forma de impachetare	13,6 cm
Greutate a doua forma de impachetare	280,0 g

Sustenabilitatea ofertei

Stare ofertă sustenabilă	Produs Green Premium
Regulamentul REACH	 Declaratia REACH
Conform REACH fara SVHC	Da
Directiva RoHS UE	Conform  Declaratia RoHS UE
Fara metale grele toxice	Da
Fara mercur	Da
Regulamentul RoHS China	 Declaratia RoHS China
Informatii privind scutirea de la RoHS	 Da
Raport de mediu	 Profilul Ambiental Al Produsului
Profil circularitate	Nu sunt necesare operatii de reciclare speciale
WEEE	În Uniunea Europeana, produsele trebuie reciclate respectand sistemul specific de colectare a deseurilor si nu trebuie sa ajunga in pubelele de colectare a deseurilor menajere.

Garantie contractuala

Garantie	18 months
----------	-----------