

Product data sheet

Characteristics

DL1BDB3

Protected LED bulb, BA 15d, green, steady light, 24 V AC/DC



Main

Range compatibility	Harmony XVB Harmony XVD Harmony XVP
Accessory / separate part designation	Protected LED bulb
Accessory / separate part type	LED bulb
Accessory / separate part category	Lighting accessories
Accessory / separate part destination	Beacon and indicator bank
[Us] rated supply voltage	24 V AC/DC
Signalling type	Steady
Signalling colour	Green
Sale per indivisible quantity	1

Complementary

Current consumption	47 mA
Bulb base	BA 15d
Net weight	0.015 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4.5 cm
Package 1 Length	6.0 cm
Package 1 Weight	11.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	60
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	987.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
 Contractual warranty	
Warranty	18 months