

Product data sheet

Characteristics

DL1BEM

Incandescent bulb, BA 15d, 7W, 230 V AC/DC



Main

Range compatibility	Harmony XVB Harmony XVD Harmony XVP
Accessory / separate part designation	Incandescent bulb
Accessory / separate part type	Incandescent bulb
Accessory / separate part category	Lighting accessories
Accessory / separate part destination	Beacon and indicator bank
[Us] rated supply voltage	230 V
Signalling type	Steady
Power dissipation in W	7 W
Sale per indivisible quantity	10

Complementary

Bulb base	BA 15d
Net weight	0.09 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.000 cm
Package 1 Width	4.800 cm
Package 1 Length	6.300 cm
Package 1 Weight	8.700 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	13.000 cm
Package 2 Width	4.800 cm
Package 2 Length	6.300 cm
Package 2 Weight	87.000 g
Unit Type of Package 3	S02
Number of Units in Package 3	240
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	2.486 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------