

Product data sheet

Characteristics

GS2AH106

Direct rotary handle, TeSys GS, black handle, front mounting, 2 positions I-O, for GS 600-800A UL



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS1 DD
Type of operating handle	Direct frontal
Handle colour	Black

Complementary

Handle positions	O-I
Rotary handle padlocking	With
Switch rated current	30 A
Standards	UL CSA
Net weight	0.04 kg

Environment

IP degree of protection	IP65
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	16.0 cm
Package 1 Length	15.0 cm
Package 1 Weight	40.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------