

Product data sheet

Characteristics

GS2AH410

External rotary handle, TeSys GS, black handle, front mounting, 2 positions I-O, NEMA 4-4X, for GS 30A Compact UL



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS1D fuse-switch disconnecter
Type of operating handle	External frontal
Handle colour	Black
Handle front plate colour	Grey

Complementary

Handle positions	O-I
Rotary handle padlocking	With
Switch rated current	30 A
Standards	UL CSA
Net weight	0.2 kg

Environment

NEMA degree of protection	NEMA 4/4X
---------------------------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	12.0 cm
Package 1 Length	14.0 cm
Package 1 Weight	220.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	20
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.893 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------