

Product data sheet

Characteristics

GS2AH570

External rotary handle, TeSys GS, black handle, front mounting, 2 positions I-O, IP65, for GS 1250A IEC



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AH
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS2V fuse-switch disconnectors FuPact FuPacT GS GSB1250 FuPact FuPacT GS GSD1250
Type of operating handle	External frontal
Handle colour	Black
Handle front plate colour	Grey

Complementary

Handle positions	O-I
Rotary handle padlocking	With
Switch rated current	1250 A
Standards	IEC
Net weight	0.39 kg





Environment

IP degree of protection	IP65
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	9.000 cm
Package 1 Length	38.000 cm
Package 1 Weight	343.900 g
Unit Type of Package 2	S01
Number of Units in Package 2	4
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.578 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------