

Product data sheet

Characteristics

GS2AHT130

External rotary handle, TeSys GS, black handle, front mounting, 3 positions Test-I-O, NEMA 3R, for GS 30-400A UL



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AHT
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS2EU TeSys TeSys GS GS2GU TeSys TeSys GS GS2JU TeSys TeSys GS GS2MU TeSys TeSys GS GS2QU
Type of operating handle	External frontal
Handle colour	Black
Handle front plate colour	Grey

Complementary

Handle positions	Test-O-I
Rotary handle padlocking	With
Switch rated current	30 A 60 A 100 A 200 A 400 A
Standards	CSA UL
Net weight	0.24 kg



Environment

NEMA degree of protection	NEMA 3R/12
---------------------------	------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	9.0 cm
Package 1 Length	18.0 cm
Package 1 Weight	240.0 g

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------