

# Product data sheet

## Characteristics

# GS2AHT140

External rotary handle, TeSys GS, red handle, front mounting, 3 positions Test-I-O, NEMA 3R, for GS 30-400A UL



## Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AHT
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS2EU[RETURN]TeSys TeSys GS GS2GU[RETURN]TeSys TeSys GS GS2JU[RETURN]TeSys TeSys GS GS2MU[RETURN]TeSys TeSys GS GS2QU
Type of operating handle	External frontal
Handle colour	Red
Handle front plate colour	Yellow

## Complementary

Handle positions	Test-O-I
Rotary handle padlocking	With
Switch rated current	30 A 60 A 100 A 200 A 400 A
Standards	UL CSA
Net weight	0.24 kg

## Environment

NEMA degree of protection	NEMA 3R/12
---------------------------	------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	9.0 cm
Package 1 Length	18.0 cm
Package 1 Weight	240.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------