

Product data sheet

Characteristics

GS2AHT420

External rotary handle, TeSys GS, red handle, front mounting, 3 positions Test-I-O, NEMA 4-4X, for GS 30A Compact UL



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AHT
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS1D fuse-switch disconnecter
Type of operating handle	External frontal
Handle colour	Red
Handle front plate colour	Yellow

Complementary

Handle positions	Test-O-I
Rotary handle padlocking	With
Switch rated current	30 A
Standards	UL CSA
Net weight	0.2 kg



Environment

NEMA degree of protection	NEMA 4/4X
---------------------------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	11.5 cm
Package 1 Length	13.0 cm
Package 1 Weight	224.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.638 kg

Offer Sustainability

RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------