

## Product data sheet

### Characteristics

## GS2AHT510

External rotary handle, TeSys GS, black handle, front mounting, 3 positions Test-I-O, IP65, for GS 32-63A IEC



### Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AHT
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS1D TeSys TeSys GS GS2F TeSys TeSys GS GS2G FuPact FuPacT GS GSB32 FuPact FuPacT GS GSC50
Type of operating handle	External frontal
Handle colour	Black
Handle front plate colour	Grey

### Complementary

Handle positions	Test-O-I
Rotary handle padlocking	Lockable in O position
Switch rated current	32 A 50 A 63 A
Standards	IEC
Net weight	0.2 kg





### Environment

IP degree of protection	IP65
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	15.0 cm
Package 1 Length	15.0 cm
Package 1 Weight	218.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.54 kg

## Offer Sustainability

REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------