

Product data sheet

Characteristics

GS2AHT540

External rotary handle, TeSys GS, red handle, front mounting, 3 positions Test-I-O, IP65, for GS 100-400A IEC



Main

Range of product	TeSys
Range	TeSys
Device short name	GS2AHT
Product or component type	Rotary handle
Range compatibility	TeSys TeSys GS GS2J[RETURN]TeSys TeSys GS GS2K[RETURN]TeSys TeSys GS GS2L[RETURN]TeSys TeSys GS GS2N[RETURN]TeSys TeSys GS GS2P[RETURN]TeSys TeSys GS GS2Q[RETURN]FuPact FuPact GS GSB100[RETURN]FuPact FuPact GS GSC125[RETURN]FuPact FuPact GS GSD125[RETURN]FuPact FuPact GS GSB160[RETURN]FuPact FuPact GS GSB200[RETURN]FuPact FuPact GS GSB250[RETURN]FuPact FuPact GS GSD250[RETURN]FuPact FuPact GS GSB400[RETURN]FuPact FuPact GS GSD400
Type of operating handle	External frontal
Handle colour	Red
Handle front plate colour	Yellow

Complementary

Handle positions	Test-O-I
Rotary handle padlocking	Lockable in O position
Switch rated current	100 A 125 A 160 A 200 A 250 A 315 A 400 A
Standards	IEC
Net weight	0.24 kg

Environment

IP degree of protection	IP65
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6 cm
Package 1 Width	15 cm
Package 1 Length	18 cm
Package 1 Weight	245 g
Unit Type of Package 2	S01

Number of Units in Package 2	6
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1.648 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------