

Product data sheet

Characteristics

GV2K011

TeSys GV2 - Emergency stop pushbutton - spring return



Main

Range	TeSys
Product name	LE GV2
Product or component type	Mushroom head emergency stop push-button
Device short name	GV2K
Accessory / separate part category	Enclosure accessory

Complementary

Product compatibility	GV2MP GV2MC LE1GVMEK
Type of operator	Spring return
Diameter	40 mm
Provided equipment	1 IP55 sealing kit
Height	48 mm
Width	73 mm
Net weight	0.052 kg
Colour	Red

Environment

IP degree of protection	IP55
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	7.500 cm
Package 1 Length	10.000 cm
Package 1 Weight	91.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.131 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------