

Product data sheet

Characteristics

GV3PC01

TeSys GV3 - Enclosure for TeSys GV3P/L - black handle - IP65



Main

Range	TeSys
Product or component type	Enclosure
Device short name	GV3PC
Accessory / separate part category	Mounting accessory
Product compatibility	GV3P GV3L
Enclosure type	Surface mounting

Complementary

Material	Metal
Rotary handle padlocking	Padlock in ON position Padlock in OFF position
Handle colour	Black
Height	312 mm
Width	181 mm
Depth	203.5 mm
Net weight	2 kg




Environment

IP degree of protection	IP65
Product certifications	UKCA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.5 cm
Package 1 Width	21.5 cm
Package 1 Length	31.5 cm
Package 1 Weight	3.642 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	60
Package 2 Height	94.5 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	231 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------