

Product data sheet

Characteristics

LE4D09V7

TeSys LE - enclosed DOL starter - 9 A - 400 V
AC coil



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE4D
Product or component type	Enclosed DOL starter
Device application	Standard
Material	Polycarbonate
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Contactor Fuse disconnecter
Motor power kW	4 KW at 380/400 V AC 50/60 Hz 4 KW at 415 V AC 50/60 Hz 4 KW at 440 V AC 50/60 Hz 2.2 KW at 220/230 V AC 50/60 Hz 5.5 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	400 V AC 50/60 Hz
[Ith] Conventional free air thermal current	9 A
Associated fuse rating	12 A 10 x 38 mm aM
Control type	Push-button start green I Push-button stop/reset red O

Complementary

Cable entry number	2 ISO20 top 2 ISO25 top 2 ISO32 top 2 ISO40 top 2 ISO20 bottom 2 ISO25 bottom 2 ISO32 bottom 2 ISO40 bottom
Width	186 mm
Height	330 mm
Depth	175.5 mm
Net weight	1.96 kg

Environment

IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment
Product certifications	UKCA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	29.000 cm
Package 1 Width	28.500 cm
Package 1 Length	46.000 cm
Package 1 Weight	3.128 kg
Unit Type of Package 2	P06
Number of Units in Package 2	6
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	29.253 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------