

Product data sheet

Characteristics

NSYBCE3

Spacial SF brush flexible cable entry gaskets -
25 mm - 300 mm enclosure



Main

Range	Spacial
Product or component type	Brush gasket
Accessory / separate part category	Cable management accessory
Device application	Multi-purpose
Range compatibility	Spacial Spacial SF suitable enclosure
Device composition	2 gasket
Quantity per set	Set of 1

Complementary

Mounting support	Cable gland plate
Cable entry	1 or 2 entries
Fixing mode	Clipped
Height	40 mm
Width	300 Mm nominal: 205 mm real:
Depth	25 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	16.5 cm
Package 1 Length	21.0 cm
Package 1 Weight	96.0 g
Unit Type of Package 2	PAL
Number of Units in Package 2	15
Package 2 Height	20.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.44 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------