

Product data sheet

Characteristics

NSYBCE4

Spacial SF brush flexible cable entry gaskets -
25 mm - 400 mm enclosure



Main

Range	Spacial
Product or component type	Brush gasket
Accessory / separate part category	Cable management accessory
Device application	Multi-purpose
Range compatibility	Spacial Spacial SF suitable enclosure
Device composition	2 gasket
Quantity per set	Set of 1

Complementary

Mounting support	Cable gland plate
Cable entry	1 or 2 entries
Fixing mode	Clipped
Height	40 mm
Width	Nominal: 400 mm Real: 305 mm
Depth	25 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	8.0 cm
Package 1 Length	30.5 cm
Package 1 Weight	142.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Logistical informations

Country of origin	FR
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------